

Flow tables for mortar and building lime

EN 459-2 | EN 1015-3 | ASTM C230 | UNI 7044 | EN 13279-2 | ASTM C1437

MAIN FEATURES

- **High resolution graphical display 128x80 pixels and 6 keys membrane keyboard**
- **8 languages can be set: Italian, English, French, Spanish, Polish, Portuguese, Romanian and Cesky**
- **Double test procedure: it is possible to set the target revolutions / drops or the total working time**

GENERAL DESCRIPTION

Used to determine the consistency of mortars and building lime. Two versions available: conforming to EN and ASTM standards, manual and motor operated.

Motor operated models are driven by a motor speed reducer and the number of drops are preset on the digital counter, which stops automatically the machine at the end of the cycle. Supplied complete with flow mould and tamper. EN versions include also the filling hopper.

TECHNICAL SPECIFICATIONS

Models	64-L0038/A	64-L0038/G 64-L0038/GY 64-L0038/GZ	63-L0040	63-L0040/A	63-L0040/G 63-L0040/GY 63-L0040/GZ
Power, W	Hand op.	180	Hand op.	Hand op.	180
Table dia. mm	300 (steel)	300 (steel)	300 (steel)	254 (bronze)	254 (bronze)
Height of drop mm	10	10	10	12.7	12.7
Total mass of movable parts, kg	4.2 to 4.5	4.2 to 4.5	4.2 to 4.5	4.08±0.05	4.08±0.05
Flow mould dim. mm	100 base 70 top 60 height (stainless steel)	100 base 70 top 60 height (stainles steel)	100 base 70 top 60 height (brass)	101.6 base 69.9 top 50.8 height (brass)	101.6 base 69.9 top 50.8 height (brass)
Dimensions mm (lpxh)	421x310x 390	50x470x 390	420x300x 410	288x254x 321	677x470x 321
Weight approx. kg	10	40	35	10	40

ORDERING INFO

Hand operated models

64-L0038/A

Hand operated flow table, conforming to EN 459-2 and EN 1015-3

63-L0040

Hand operated flow table, conforming to UNI 7044

63-L0040/A

Hand operated flow table, conforming to ASTM C230

Motorized models

64-L0038/G

Motor operated flow table, conforming to EN 459-2 and EN 1015-3. 230 V, 50 Hz, 1 ph.

64-L0038/GY

Motor operated flow table, conforming to EN 459-2 and EN 1015-3. 220 V, 60 Hz, 1 ph.

64-L0038/GZ

Motor operated flow table, conforming to EN 459-2 and EN 1015-3. 1100 V, 60 Hz, 1 ph.

63-L0040/G

Motor operated flow table, conforming to ASTM C230. 230 V, 50 Hz, 1 ph.

63-L0040/GY

Motor operated flow table, conforming to ASTM C230. 220 V, 60 Hz, 1 ph.

63-L0040/GZ

Motor operated flow table, conforming to ASTM C230. 110 V, 60 Hz, 1 ph.

ACCESSORIES

Accessories

63-L0037/1

Flow caliper to EN 459-2 and EN 1015/3

63-L0040/1

Flow caliper to ASTM C230

Spare parts

63-L0038/10

Stainless steel flow mould to EN 459-2, EN 1015/3

63-L0037/10

Brass flow mould to UNI 7044

63-L0040/10

Brass flow mould to ASTM C230

63-L0037/11

Tamper to EN 459-2 and EN 1015-3

63-L0037/12

Filling hopper for 63-L0037/10 and 63-L0038/10 flow moulds

63-L0040/11

Hardwood tamper 12x25x150 mm to ASTM C230



Motor operated flow table,
conforming to EN 459-2 and EN
1015-3, model 64-L0038/Gx



Hand operated flow table,
conforming to ASTM C230 model
63-L0040/A



Motor operated flow table,
conforming to ASTM C230 model
63-L0040/Gx



Flow caliper to EN 459-2 and EN
1015/3 model 63-L0037/1



Flow caliper to ASTM C230 model
63-L0040/1

Array